

## STANDARD OFFER 1800LXA WASHER DRYER

### MAIN SPECIFICATIONS

- Double chamber, big washing capacity
- Sliding downwards glass door
- Chamber and injectors drying through HEPA filtration
- Chamber, frame in AISI 316L stainless steel
- Side, rear, top panels in AISI 304L stainless steel
- Telescopic rails for quick & easy loading and unloading
- Microprocessor control : up to 42 programs with 53 adjustable parameters
- 4 pre-set application programs :
  - \* chemistry glassware
  - \* volumetric glassware (low temperature)
  - \* bacteriology/virology (high temperature)
  - \* stubborn stains (Agar)
- 2 line alphanumeric display
- Useful chamber dimensions : 770 x 1064 x 510 mm
- Chamber volume : 417 litres
- External dimensions : 1983 x 1338 x 825 mm
- Weight : 365 kg
- 1 to 6 washing levels with 8 possible positions
- Washing on one to six independent levels using fully interchangeable jet racks or rotary arm baskets for multiple loading configurations
- Powerful hydraulic circuit with Direct Water Injection on each washing level
- Automatic dosing of liquid chemicals by means of 2 peristaltic pumps (detergent and acid)
- 2 separate inlets for cold and demineralized water
- Integrated automatic door locking system
- 400V - 3 Phases + Earth + Neutral - 50 Hz
- Other voltage on request



## STANDARD OFFER 1800LXA WASHER DRYER

### MAIN OPTIONS

- Steam condenser removes steam vapour when chamber temperature exceeds 50°C and directs all condensate to the drain (90010510)
- Low pressure valve + pump (01060206)
- Chemical's level detection (01060225)
- Softener (90010328)
- Drain temperature cool down option to cool down the waste water under 60°C (90010501)
- RS 232 Output (90010463)
- External printer for RS 232 output (90010474)
- MONVAL validation monitor (01060195)

### ACCESSORIES

#### ***Optimized three level configuration***

- 1 x PST : Basic basket (02010040)
- 1 x LT 1/3 : Stainless steel grid basket for long test tubes (02010033)
- 1 x PST : basic basket (02010040)
- 1 x 48 IXLC : 48 jet rack tall + low diam 6 (01030185)
- 1 x 48 IXC : 48 jet rack low diam 6 (01030183)
- 1 x 64 IXC : 64 jet rack low diam 6 (01030188)
- 1 x 36 IXLC : 36 jet rack tall + low diam 6 (01030182)

#### ***Optimized 2 level multi purpose configuration***

- 1 x 48 IXLC : 48 jet rack tall + low diam 6 (01030185)
- 1 x 36 IXLC : 36 jet rack tall + low diam 6 (01030182)
- 1 x 25PIP/30IXLC : 25 pipette + 30 jet rack tall + low (02010087)
- 1 x 48 IXC : 48 jet rack low diam 6 (01030183)

#### ***Optimized 2 level multi purpose configuration***

- 1 x 48 IXLC : 48 jet rack tall + low diam 6 (01030185)
- 1 x PSBT : basic basket + arm (02010043)
- 1 x 100 PIP : 48 short injector for narrow neck glassware (02010085)
- 1 x 36 IXLC : 36 short and long injectors (01030182)

### **Optimized configuration for pipette and measuring cylinders**

- 1 x 4EP/25IXLC : rack for 4 measuring cylinders and glassware (02010005)
- 1 x 100 PIP : 48 short injector for narrow neck glassware (02010085)
- 1 x 36 IXLC : 36 short and long injectors (01030182)

### **SALES CONDITIONS**

- PACKING
- DELIVERY TIME : 8-10 WEEKS AFTER RECEIPT OF YOUR ORDER
- VALIDITY OF THE OFFER : 3 MONTHS
- PAYMENT : ADVANCE PAYMENT

**NET TOTAL EX WORKS TOURNEFEUILLE**